

PSE

Compact Panel Mount Hall-Effect Rotary Sensor





True, contactless operation

Without any gears or mechanical interfaces the sensor is easily assembled and calibrated and subject to limited wear and tear over lifetime.



Durable and robust design

The non-contacting design allows for an extra-long product lifetime of up to 50 million cycles.



Integrated shaft

The magnet is securely fastened to the shaft and acts as only moving component in the sensor.



Made for harsh environments

The rugged package protects the sensor from dust, moisture, vibration and extreme temperatures for usage in the most demanding environments.



Adaptable to your requirements

Custom mechanical design, programmable transfer function as well as different output protocols and redundancy levels available.

DESCRIPTION

Piher Sensing Systems' PSE Series Rotary Position Sensors are based on contactless hall-effect technology and deliver high accuracy and linearity in a compact package. Increased rotational life and robustness against humidity, vibration and shock make them perfectly suited for harsh industrial and transportation environments. These absolute sensors will not lose its values even after a power failure

The PSE end-of-shaft sensor is offered in two versions: one with 360 degree endless rotation with programmable electrical angles from 15 to 360 degrees (without deadband) and another version that stops the rotary movement at rotational travel of 290 degrees.

Custom versions with different shafts and customer specific output curves can be delivered on request.

APPLICATIONS

Industrial

- ▶ Autonomous warehouse robotics
- Robotics and automation feedback
- ▶ Valve monitoring
- Paint spray systems
- ▶ Conveyor operation
- Test and measurement equipment
- ► Machine tool control

Transportation

- ▶ Steering wheel angle
- Pedal Position
- ► Suspension/height detection
- Fork height and mast tilt
- ▶ Bucket position
- ► Hitch position
- ► Transmission gear shift
- Cab controls

Marine

▶ Steering and shifter sensor

Home and Building Automation

► HVAC systems

Medical

▶ Equipment control

PSE

Compact Panel Mount Hall-Effect Rotary Sensor

MECHANICAL SPECIFICATIONS		
Mechanical Angular Range	360° endless rotation (PSE-360) 290° (PSE-290)	
Connection	Fly leads, connector assembly on request	
Rotational life	50.000.000 cycles	
Shaft diameter	6,25mm	
Mounting Method	Panel mount	
Rotational torque	1Ncm	

Other specifications on request


ELECTRICAL SPECIFICATIONS		
Linearity ¹	±1% absolute (±0.5% upon request)	
Electrical Angular Range ²	360°, 270°, 180°, 120°, 90°, 50°	
Output Protocol	Analog (Ratiometric), PWM	
Resolution	12 bits	
Output Range ² standard inverted	10% to 90% Vdc 90% to 10% Vdc	
Supply Voltage ²	5V ±10%	
Supply Current	Typ 8.5 mA	
Voltage Protection	±18V	
Self-diagnostic features	yes	


 $^{^{\}rm I}$ Ferromagnetic materials close to the sensor (i.e. shaft, mounting surface) may affect the sensor's linearity. $^{\rm 2}$ Other specification on request

ENVIRONMENTAL SPECIFICATIONS		
Operating temperature ¹	-40° to +80°C	
Shock	according to SHOCK MIL-STD-202F Method 213B Test Condition C	
Vibration	according to MIL-STD-202F Method 204D Test Condition B	
Humidity	according to MIL-STD-202F Method 103B Test Condition A	
EMI / ESD	according to UNE-EN 61000-4-2:2010 +/-6kV DC; +/-8kV AC	

¹Other specifications available

DIMENSIONS (MM)





Cable color	Function	Pin
Brown	Vcc	1
Black	Out	2
Blue	Gnd	3


 ↑ The sensor is shipped with one nut installed at its base. An assembled washer and an extra nut are available upon request. Other shafts are also available upon request.









Compact Panel Mount Hall-Effect Rotary Sensor



- 1 The analog output is ratiometric, proportional to input voltage.
- 2 Other electrical angular ranges available on request.
- 3 Other output functions available on request. Enter X as long as the new output function is not defined.
- 4 Leave empty if not applicable. Others available on request.



- 1 Other mechanical and/or electrical angular ranges available on request.
- 2 The analog output is ratiometric, proportional to input voltage
- 3 Other output functions available on request. Enter X as long as the new output function is not defined.
- 4 Leave empty if not applicable. Others available on request.




Custom output functions available on request.

Compact Panel Mount Hall-Effect Rotary Sensor

PSE-290 TYPICAL OUTPUT CURVE

ERA-270



Custom output functions available on request.

MECHANICAL CUSTOMIZATION OPTIONS

- Different shaft sizes
- Additional O-rings
- Connector assembly
- Heat shrink wire protectors













Please always use the latest updated datasheets and 3D models published on our website.

Disclaimer:
The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information.
Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf [collectively, "Piher"], disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein provided herein to the maximum extent permitted by law. Drawings are not necessarily to scale. Some elements may be shown at different scales for claim, The product specifications do not expand or or therwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which apply to these products. Not license, express or implied, by estopped or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher.

The products hown herein are not designed for use in medical, life-assing, or life-austaining applications unless otherwise expressly indicated. Customers using or selling Piher products not expressly indicated for use in such applications of so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting from such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this catalogue may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information contained in and/or attached to this catalogue may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information

CONTACT

Piher Sensing Systems

Polígono Industrial Municipal Vial T2, N°22 31500 Tudela Spain

sales@piher.net

+34 948 820 450



NEED QUICK HELP?

Our Al Virtual Assistant is available 24/7 to provide instant support visit chat.piher.info to chat now!

